




Stainless and Aluminum Gate Valves



Aluminum valves with (left to right): Electro Pneumatic, Manual, and Motor Actuators. Stainless Steel valves also available.

ANSI, ISO, JIS, or Special Flanges

These Vacuum Research 5 minute rebuild valves are available with virtually any flange or combination of flanges at no extra charge. Combinations of ISO on one flange and ANSI on the other are easily accommodated. Even different sizes such as 4 inch on one flange and 6 inch on the other.

Insertable "Flangeless" Valves

It is sometimes helpful to keep the flange to flange dimension ("A" dimension on the dimensions pages) as short as possible. In such cases your valves can be provided with no port flanges at all and with either O-Ring grooves machined into the valve body or with a precision machined surface on the body to seal against the O-rings on your pump or chamber. Contact the factory for prices.

Aluminum or Stainless Steel

Vacuum Research Bonnet Style valves are available in stainless steel or 6061 aluminum. Smooth surface finish gives low outgassing and fast pump down.

High Conductance

In addition to the oversize ports used in the LPWA Series for the last 40 years, we now offer the X-LPWA Series where a 4 inch valve has a 6 inch port, an 8 inch valve has a 10 inch port, etc. Conductance values are shown on page 43.

Fail Safe

All Vacuum Research Valves can be installed for fast close on power failure and air operated valves can be manually positioned without air or electricity.

Long Life

More than 250,000 cycles for aluminum valves. That's one cycle every 2 minutes, 24 hours/day for a year. An optional million cycle design is available.

Satisfaction Guaranteed

Vacuum Research has been building high vacuum valves for almost 50 years and has earned a reputation for world class product quality and customer service. If you are not satisfied with our valve just send it back.

Fast Repair

In under 5 minutes you can replace every moving part in a Vacuum Research Bonnet Style valve with no special tools or training. The valve port stays in your system to support the pump and vacuum lines.

Vacuum & Pressure

Vacuum Research Valves stay sealed against positive pressure in either direction.

No Leaks

All Vacuum Research valves have total leak rates of less than 5×10^{-10} std cc/sec. By total leak we mean that each completed valve is tested in a He filled bag.

RoHS Compliant

All Valves (RoHS) 2002/95/EC Compliant

Electric Motor, Air or Manual Actuators

All Vacuum Research gate valves are available with 3 types of actuators. Manual actuators are the least expensive. Electro-pneumatic actuators use 70 psi (4.9 kg/cm) compressed air and include the solenoid (specify the solenoid voltage that is most convenient for you). Electric motor actuators use high torque servo motors and operate from 115V or 230V, 1Ø 50 or 60 Hz. CE Mark included.

Roughing and Gauge Ports

There are six locations for optional gauge and roughing ports described on page 44.

Position Indicators, Limit Switches


Visual position indication of valve position is included on all valves. Limit switches for remote indication are described on the Optional Features pages in the Accessories & Parts section.



Complete Rebuild


in 5 Minutes!

With no special tools or training you can replace every moving part in your Vacuum Research Bonnet Style Valve in 5 minutes. (Our best guys can do it in less time, but they practice.)



- 250,000 Cycle Rotary Shaft Seal
- Million Cycle Valves Also Available
- Large Port, Mates With JIS Flanges
- 6 Optional Roughing Port Locations
- Easy to Service, 2-Piece Bonnet Design
- Helium Leak Less Than 5×10^{-10} scc/sec
- All Valves (RoHS) 2002/95/EC Compliant
- Fail Safe Design, Close On Power Loss
- Vacuum & Pressure; Optional Seal to 3 ATM.
- Optional Operation to 10 Bar, 147 PSIG

N1 Tapped Holes Both Sides **N5** Neck on Both Sides **N6** Neck on Seal Side **N8** Neck Opposite Seal Side



The gate seal O-ring is on the actuator side (to left) in aluminum valve sizes from 80 through 200 mm. The gate seal is on the side opposite the actuator on 250 & 300 mm aluminum and stainless steel valves.

ORDERING INFORMATION

Model Number: Refer to page 2 for instructions on how to specify the features you need.

Electric Motor Actuators: Any Vacuum Research valve can be supplied with a high torque electric motor actuator. Refer to "Electric Motor Actuator" Page in the Accessories and Parts section.

Special Features: Refer to pages 44-46 for specifications for roughing and gauge ports, position indicators & other special features.


Viton® or Kalrez® or Silicone O-Rings All of our standard Valves use a Viton® O-Ring for the gate seal and Buna-N O-Rings for all other locations. You may specify Viton® or other materials throughout the valve with a "V" in the model number and add the following to the price.

65 or 80 mm valves . . . \$38.	200 mm valves . . . \$119.
100 mm valves . . . \$57.	250 mm valves . . . \$136.
150 mm valves . . . \$74.	300 mm valves . . . \$179.


(Use "S" for Silicone, "K" for Kalrez®, and contact the factory for prices.)

JIS Gate Valves

Nominal Size	Electro-Pneumatic Operator "EP" Suffix				Manual Operator "M" Suffix			
	Aluminum Model & Neck Style		Stainless Steel Model & Neck Style		Aluminum Model & Neck Style		Stainless Steel Model & Neck Style	
		Price		Price		Price		Price
65 mm One piece style	OP-65-JIS-N1-EP	\$1086.	OPSS-65-JIS-N1-EP	\$2023.	OP-65-JIS-N1-M	\$903.	OPSS-65-JIS-N1-M	\$1723.
	OP-65-JIS-N5-EP	\$1610.	OPSS-65-JIS-N5-EP	\$2258.	OP-65-JIS-N5-M	\$1095.	OPSS-65-JIS-N5-M	\$1957.
	OP-65-JIS-N6-EP	\$1182.	OPSS-65-JIS-N6-EP	\$2141.	OP-65-JIS-N6-M	\$1000.	OPSS-65-JIS-N6-M	\$1840.
	OP-65-JIS-N8-EP	\$1182.	OPSS-65-JIS-N8-EP	\$2141.	OP-65-JIS-N8-M	\$1000.	OPSS-65-JIS-N8-M	\$1840.
80 mm	LPWA-80-JIS-N1-EP	\$1436.	LPSS-80-JIS-N1-EP	\$2156.	LPWA-80-JIS-N1-M	\$1275.	LPSS-80-JIS-N1-M	\$1806.
	LPWA-80-JIS-N5-EP	\$1590.	LPSS-80-JIS-N5-EP	\$2410.	LPWA-80-JIS-N5-M	\$1485.	LPSS-80-JIS-N5-M	\$2060.
	LPWA-80-JIS-N6-EP	\$1545.	LPSS-80-JIS-N6-EP	\$2301.	LPWA-80-JIS-N6-M	\$1385.	LPSS-80-JIS-N6-M	\$1950.
	LPWA-80-JIS-N8-EP	\$1545.	LPSS-80-JIS-N8-EP	\$2301.	LPWA-80-JIS-N8-M	\$1385.	LPSS-80-JIS-N8-M	\$1950.
100 mm	LPWA-100-JIS-N1-EP	\$1484.	LPSS-100-JIS-N1-EP	\$2735.	LPWA-100-JIS-N1-M	\$1325.	LPSS-100-JIS-N1-M	\$2310.
	LPWA-100-JIS-N5-EP	\$1640.	LPSS-100-JIS-N5-EP	\$3025.	LPWA-100-JIS-N5-M	\$1480.	LPSS-100-JIS-N5-M	\$2565.
	LPWA-100-JIS-N6-EP	\$1568.	LPSS-100-JIS-N6-EP	\$2880.	LPWA-100-JIS-N6-M	\$1410.	LPSS-100-JIS-N6-M	\$2460.
	LPWA-100-JIS-N8-EP	\$1568.	LPSS-100-JIS-N8-EP	\$2880.	LPWA-100-JIS-N8-M	\$1410.	LPSS-100-JIS-N8-M	\$2460.
150 mm	LPWA-150-JIS-N1-EP	\$1615.	LPSS-150-JIS-N1-EP	\$3180.	LPWA-150-JIS-N1-M	\$1445.	LPSS-150-JIS-N1-M	\$2820.
	LPWA-150-JIS-N5-EP	\$1849.	LPSS-150-JIS-N5-EP	\$3470.	LPWA-150-JIS-N5-M	\$1680.	LPSS-150-JIS-N5-M	\$3100.
	LPWA-150-JIS-N6-EP	\$1734.	LPSS-150-JIS-N6-EP	\$3400.	LPWA-150-JIS-N6-M	\$1566.	LPSS-150-JIS-N6-M	\$3040.
	LPWA-150-JIS-N8-EP	\$1734.	LPSS-150-JIS-N8-EP	\$3400.	LPWA-150-JIS-N8-M	\$1566.	LPSS-150-JIS-N8-M	\$3040.
200 mm	LPWA-200-JIS-N1-EP	\$3133.	LPSS-200-JIS-N1-EP	\$4230.	LPWA-200-JIS-N1-M	\$2912.	LPSS-200-JIS-N1-M	\$3760.
	LPWA-200-JIS-N5-EP	\$3405.	LPSS-200-JIS-N5-EP	\$4535.	LPWA-200-JIS-N5-M	\$3181.	LPSS-200-JIS-N5-M	\$4050.
	LPWA-200-JIS-N6-EP	\$3229.	LPSS-200-JIS-N6-EP	\$4445.	LPWA-200-JIS-N6-M	\$3005.	LPSS-200-JIS-N6-M	\$3975.
	LPWA-200-JIS-N8-EP	\$3229.	LPSS-200-JIS-N8-EP	\$4445.	LPWA-200-JIS-N8-M	\$3005.	LPSS-200-JIS-N8-M	\$3975.
250 mm	LPWA-250-JIS-N1-EP	\$3777.	LPSS-250-JIS-N1-EP	\$6775.	LPWA-250-JIS-N1-M	\$3518.	LPSS-250-JIS-N1-M	\$5930.
	LPWA-250-JIS-N5-EP	\$4078.	LPSS-250-JIS-N5-EP	\$7350.	LPWA-250-JIS-N5-M	\$3820.	LPSS-250-JIS-N5-M	\$6510.
	LPWA-250-JIS-N6-EP	\$3927.	LPSS-250-JIS-N6-EP	\$7135.	LPWA-250-JIS-N6-M	\$3670.	LPSS-250-JIS-N6-M	\$6290.
	LPWA-250-JIS-N8-EP	\$3927.	LPSS-250-JIS-N8-EP	\$7135.	LPWA-250-JIS-N8-M	\$3670.	LPSS-250-JIS-N8-M	\$6290.
300 mm	LPWA-300-JIS-N1-EP	\$4693.	LPSS-300-JIS-N1-EP	\$8940.	LPWA-300-JIS-N1-M	\$4435.	LPSS-300-JIS-N1-M	\$8095.
	LPWA-300-JIS-N5-EP	\$4982.	LPSS-300-JIS-N5-EP	\$9520.	LPWA-300-JIS-N5-M	\$4720.	LPSS-300-JIS-N5-M	\$8820.
	LPWA-300-JIS-N6-EP	\$4825.	LPSS-300-JIS-N6-EP	\$9400.	LPWA-300-JIS-N6-M	\$4565.	LPSS-300-JIS-N6-M	\$8675.
	LPWA-300-JIS-N8-EP	\$4825.	LPSS-300-JIS-N8-EP	\$9400.	LPWA-300-JIS-N8-M	\$4565.	LPSS-300-JIS-N8-M	\$8675.



Vacuum Research valves are available with dozens of options to allow you to select exactly the features you need for your vacuum system. The model number system illustrated below will accurately describe most valves, but if you have any questions about the best way to specify what you need, just call or fax our customer service department and we will be happy to help you. All Valves (RoHS) 2002/95/EC Compliant



Ordering Information



Call our toll free number (800) 426-9340, or (412) 261-7630 to place orders, or for customer service.



Our FAX number is (412) 261-7220. Address orders by mail to Vacuum Research Corporation, 2419 Smallman Street, Pittsburgh, PA 15222 USA. Prices in this catalog are FOB factory. CIF or C&F prices available. Contact factory for pro forma invoice or price quotation. Terms are Net 30 Days.



Kalrez® and Viton® are registered trademarks of Dupont Corp. • Conflat® is a registered trademark of Varian Associates • Throttlemaster™ is a registered trademark of Vacuum Research Corporation

Vacuum Research Corp. • 2419 Smallman Street • Pittsburgh, PA 15222 USA • www.vacuumresearch.com

Phone: 800-426-9340 • 412-261-7630 • FAX: 412-261-7220 • e-mail: VRC@vacuumresearch.com